

New De-Ionised Water

De-Ionised Water

Conforms to BS4974. Purified of dissolved minerals and salts through de-ionisation and recognised as the best choice for maintaining lead acid batteries.

- Does not conduct electricity and will not hinder battery performance

Part No.	Qty	Size
VC805	1	5 Litre
VC825	1	25 Litre

*Battery not included or supplied - for illustration purposes only



PRESSOL Funnel with Flexible Spout
Polyethylene with removable brass filter.

Part No.	Qty	Diameter
FUN6	1	160 mm (6.4")



PRESSOL Small Funnels Set
Polythene.

Part No.	Qty	Description
FUN7	1 Set	5 Piece Set

5 x Sizes: Ø 60, 80, 100, 120, 140 mm.



Measuring Jugs
Complete with lid and removable spout with stopper.

Part No.	Qty	Capacity
JUG31	1	1 Litre
JUG32	1	2 Litre
JUG33	1	5 Litre